

Quantec master infrared ceiling receiver

Part No. **QT302RX**



Overview

Designed to accept infrared calls from compatible Quantec staff attack transmitters, patient neck/wrist pendants and staff attendance pendants. Typically used in bedrooms, corridors, common rooms and any other area requiring infrared coverage. Include a red confidence light. Typical 10m line of sight receiving range. Up to three QT302RXS slave receivers can be connected to a master ceiling receiver to increase IR coverage.

Technical Specifications

Power requirements	Nominal 24V DC (from Quantec Controller/Network).
Quiescent current	Less than 3mA.
Alarm current	14mA.
Indicators	Red/green confidence LED.
Controls	n/a.
Connections	Net +; Net -; R; G; L+; SW; IR; SLV.
Expansion connections	R; G; L+; SW; IR & SLV terminals allow the connection of optional slave overdoor lights and slave infrared receivers.
Onboard 6.35mm Remote Jack Socket	No.
Onboard Sounder	No.
Onboard Infrared Receiver	Yes - will accept calls from compatible Quantec infrared transmitters.
Product dimensions (mm)	87 W x 87 H x 19 D mm. Can be mounted on a standard UK 25mm single gang flush or surface back box.
Construction & finish	Plastic.
IP Rating	IP40.
Weight	64g



Operating conditions/temperature

-5°C to +40°C. Max relative humidity: 95%.



T 01942 322744 E sales@c-tec.co.uk
F 01942 829867 W www.c-tec.com



C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom



T 01942 322744 E sales@c-tec.co.uk
F 01942 829867 W www.c-tec.com



C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom